

**PRODUCT: Solid Flocculant**

**EDITION:** February 2008

**REVISION:** 3 – February 2015

**SPECIFICACIONES**

CHARACTERISTICS	VALUE	UNITS	METHOD*
Richness (as Al <sub>2</sub> O <sub>3</sub> )	16,0 min.	% p/p	DS01PF02.3100

(\*) The Company's internal procedures are based party or fully on analytical reference methods (ISO, ASTM).

**TYPICAL VALUE**

Aspect    Tablets into 125g sacks.

**OTHERS**

**Applications :**

Product for the flocculation of impurities and of water cloudiness, thereby improving it's transparency. **NOT TO USE IN DIATOM FILTERS.**

**Treatment :**


Wash filter in countercurrent and place in the skimmer or prefilter two flocculant sacks for each 100 m<sup>3</sup> of water.  
 Repeat the procedure each two filter washings or twice at month, according to water turbidity.

For further information, please refer to the material safety data sheet.


**USUAL PACKAGING**

As per customer order.

APPROVED BY QUALITY FACTORY



APPROVED BY COMMERCIAL MANAGEMENT



PGC.E.01.F01  
 (PGC.E.01 - Rev. 7)